

The smooth thing ... a hotmelt cartridge with easy slide coating

KLEIBERIT 782 Supramelt



PRODUCT INFORMATION



Advantages of the easy slide coating:

· Protected from dust

The cartridge is protected from contamination, dust and dirt whilst being stored at the work place. In addition to this even if stored in a warm environment the cartridges do not stick together.

· Problem free melting

The new foil coating acts like a lubricant when in the machine. It aids smooth problem free melt rate and dissolves without trace during the melting process.

Increased melting speed

The cartridge with the easy slide coasting ensures increased melting speed, which is required to bond wide edges and long substrates.

• Easy change of cartridges


When colour changes are required, the cartridges can be taken out and used again easily, as the foil protects the cartridge.



KLEBCHEMIE

M. G. Becker GmbH & Co. KG Max-Becker-Str. 4 76356 Weingarten GERMANY

Phone: +49 7244 62-0 Fax: +49 7244 700-0 www.kleiberit.com



11/2016

Copyright © by KLEIBERIT - Brandname of KLEBCHEMIE GmbH & Co. KG



FIELD OF APPLICATION

Bonding of

- Epoxy resin edges
- Pre-primered ABS edges
- · Solid wood edges
- Polyester edges
- Pre-primered PVC-edges
- Veneer edges

APPLICATION

- Both substrates have to be cut to an exact right angle and must be free from dust.
- Bring the substrate and the edging material up to room temperature
- The ideal moisture content of the wood is 8-10%, room temperature of min. 18 °C, avoid drafts
- Pre heat time 2-5 minutes, application temperature 200-220 °C
- Correct temperature settings are especially important when bonding solid wood edges
- When bonding long and/or ridged pieces the application temperature should be in the higher temperature areas.
- Lower temperatures reduce the "wetting out" of the edges
- Coat weight and press pressure should be adjusted so that the applied beads are pressed flat and the adhesives quills out on the edges slightly. To determine the correct coat weight the use of a transparent edge is advised.

NOTE

- For solid wood edging the use of linear grain wood is preferable as this is less prone to bend.
- To achieve optimum bond strength the wood grain of the edges should be vertical on the bond surface.
- Precisely align the edging material
- The chipboard should have a surface which does not have rough cutting marks.
- The easy slide coating does not need to be removed prior to processing.

IDENTIFICATION

Identification is not required to EU regulation

When hotmelt adhesive are melted and applied, vapours are set free and an unpleasant odour can occur, even is the recommended working temperature has been observed. If the recommended working temperature is exceeded over a long period of time, harmful decompositon products can develop. Precautions should be taken i.e. using suitable ventilation, to eliminate vapours.

Please observe our data sheet 782 GL

TECHNICAL PROPERTIES

• Basis Ethylene-Vinylacetate-Copolymer

Specific gravity approx. 1.3 g/cm³
 Softening point (Ring and Ball) DIN 1995

120 °C ± 10 °C

• Melting index DIN 53 735 (MFI 150/2.16)

60 c 15 g/10 min.

Pre heat time 2 - 5 minutes
 Speed 8 - 20 m/min.,

depending on machine

Heat resistance
 Cold resistance
 to +80 °C depending on edge
 to -20 °C depending on edge

• Colours white

white (10) ivory (20) mahogany (70) black (99)

• Packaging cartridge

Ø: $63 \pm 0.5 \text{ mm}$ length: $80 \pm 2.0 \text{ mm}$

CLEANING

When cleaning the application equipment observe the manufacturers instructions.

DISPOSAL

Hardened adhesive domestic waste disposal
Our packaging is made from recyclable materials.

PACKING SIZES

Carton with 45 cartridges, approx. 15 kg net.

STORAGE

KLEIBERIT 782 Supramelt

Can be stored for approx. 2 years
Store cool, dry and in original sealed packaging.

TECHNICAL DATA

Supramelt



SERVICE

Our application department may be consulted at any time without obligation. The statements here-in are based on our experience gained to date. They are to be considered as information without obligation. Please test and establish for yourself the suitability of our products for your particular purposes. No liability exceeding the value of our product can be derived from the foregoing statements. This also applies to the technical consultancy service, which is rendered free of charge and without obligation.